

## **Bovone 200 Series – Tooling Setup**



MACHIN MATERIA	ES: 200 Series AL: Clear Glass and Mirror	PROCESS: SETS:	Bevel Standard and Premium	REMA		Standard and Premion General Application	um Tools for
POS		DESCRIPTIO	N		STA	NDARD PART #	PREMIUM PART #
1	Diamond Cup Wheel – Metal ( 150x45x22ah	continuous)				DC1A	DC1DC
2	Diamond Cup Wheel – Metal ( 150x45x22ah	continuous)				DC2A	DC2DC
3	Diamond Cup Wheel – Resin ( 150x45x22ah	solid)				DC3RA	DC3RC
4	Diamond Cup Wheel – Resin ( 150x45x22ah	solid)				DC5A	DC5HC
5	Diamond Cup Wheel – Resin ( 150x45x22ah	solid)				DC6A	<b>DC6HC</b>
6	Diamond Peripheral Wheel (p 150x22ah   6 mm groove	encil edge)				DP616A	DP700C
7	Polishing Wheel – NOVAFelt F 150x25x70ah	elt		Ô-	FN6P	FN6* * (ready-mount)	FN6* FN6P* (ready-mount)
8	Polishing Wheel – NOVAFelt F 185x25x115ah	elt		Ô	FN7P	FN7* * (ready-mount)	FN7* FN7P* (ready-mount)

Additional options available. Contact Salem for more information.

Wheels pictured are from our premium tooling line.

## GO BEYOND THE EDGE

<sup>\*</sup>Axion glass polish is recommended for use with felt wheels on Bovone machines.