

KODIAK® 371 – Tooling Setup





| MACHIN MATERIA | | PROCESS: SET: | Bevel Premium | REMARKS: | Premium To | ools for General Application |
|-------------------|---|------------------|------------------|----------|--------------|----------------------------------|
| POS | | DI | ESCRIPTION | | | PREMIUM PART # |
| 1 | Diamond Cup Wheel – Metal 150x45x22ah | (continuous) | | | | DC1DC |
| 2 | Diamond Cup Wheel – Metal 150x45x22ah | (continuous) | | | | DC2DC |
| 3 | Diamond Cup Wheel – Resin (150x45x22ah | solid) | | | | DC3RC |
| 4 | Diamond Cup Wheel – Resin (150x45x22ah | solid) | | | 0 | DC4HC |
| 5 | Diamond Cup Wheel – Resin (150x45x22ah | solid) | | | | DC5HC |
| 6 | Diamond Cup Wheel – Resin (150x45x22ah | solid) | | | | DC6HC |
| 7 | Diamond Cup Wheel – Resin (150x45x22ah | solid) | | | | DC7HC |
| 8 | Diamond Peripheral Wheel (150x22ah 6 mm groove | pencil edge) | | | | DP700C |
| 9 | Polishing Wheel – NOVAFelt F 150x25x70ah | elt | | | (5 - | FN6 FN6P (ready-mount) |

Additional options available. Contact Salem for more information.

Wheels pictured are from our premium tooling line.


Tooling setup continued on next page.

GO BEYOND THE EDGE

Office: 724.212.3749



KODIAK® 371 – Tooling Setup (Continued)





| MACHIN MATERIA | E: KODIAK® 371 AL: Clear Glass and Mirror | PROCESS: SET: | Bevel Premium | REMARKS: | Premium 1 | Fools for General Application |
|-------------------|--|------------------|------------------|----------|---------------------------|-------------------------------|
| POS | | D | ESCRIPTION | | | PREMIUM PART # |
| 10 | Polishing Wheel – NOVAFelt 150x25x70ah | | | | FN6 FN6P (ready-mount) | |
| 11 | Polishing Wheel – NOVAFelt 150x25x70ah | Felt | | | () | FN6 FN6P (ready-mount) |

Additional options available. Contact Salem for more information.

Wheels pictured are from our premium tooling line.

GO BEYOND THE EDGE